Specifications	
Pressure range	4 to 20 cm H ₂ O
Mode	Auto
Flex setting	1 (Off); 1 (On)
Ramp time	0 to 45 min (5-min increments)
Starting ramp pressure	Patient adjustable
Dimensions	7" L x 5.5" W x 4" H; 18 cm L x 14 cm W x 10 cm H
Weight	1.53kg (3.37 lbs) (without humidifier)
Filters	Foam and optional ultra-fine
Device setup	LED/keypad
Data storage capacity	Compliance VIC 7-30-day averages
	On-board: > 1 year
	SD Card (optional): lifetime
Compliance meter	Breathing detection
Altitude compensation	Automatic
Electrical requirements	100-240 VAC, 50/60 Hz, 2.1A
Humidification	Integrates with System One heated humidifier
Humidification modes	Classic
Warranty	Two years

Auto CPAP

Dorma 500

Accessories		
Humidification, t	ubing and replacement components	
IN6H	Heated humidifier	
1063785	Water chamber	
1032907	6 ft. performance tubing 22 mm	
1063857	Carrying case	
1099592	Device side panel	
1091398	60 watt power supply	
1039026	Power cord UK	
1039014	Power cord Europe	
1035443	Reusable foam Filter (pack of 1)	
1029330	Reusable foam Filter (pack of 2)	
1063096	Disposable filter (pack of 1)	
1035442	Disposable filter (pack of 2)	
1029331	Disposable filter (pack of 6)	
Connectivity		
1063859	SD card (pack of 10)	
1065146	SD card mailer (pack of 10)	
1081105	SD card mailer (pack of 10) Padded	
1063858	SD card cover replacement	
1047300	SD card reader	
1073915	Sleep therapy SD card reader	
1061644A	Philips Respironics Link Module	

INV501 Dorma 500 INV501H Dorma 500 Auto with humidifier

Dorma 500 advantages

- Auto titrating
- Quiet operation
- · Flex pressure relief
- · Integrated heated humidifier
- · Encore compatible

© 2014 Koninklijke Philips N.V.All rights are reserved.

Philips Healthcare is part of Royal Philips

Philips Healthcare reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

